


AF09 ... AF96 2-stack 3-pole contactors

Main accessories

Contactor and main accessories (other accessories available)



Main accessory fitting details

Many configurations of accessories are possible depending on whether these are front-mounted or side-mounted.

Contactor types	Main poles		Built-in auxiliary contacts		Front-mounted accessories					Side-mounted accessories		
					Auxiliary contact blocks				Electronic timer	Electrical and mechanical interlock set (between 2 contactors)		Auxiliary contact blocks
					1-pole CA4 1-pole CC4	2-pole CAT4-11	4-pole CA4	TEF4	VEM4	Left side 2-pole CAL4-11	Right side	
AF26 ... AF38	3	0	1	1	–	–	–	–	–	+	1	+ 1
AF40 ... AF65	3	0	1	1	4 max.	or 1	or 1	or 1	–	–	–	+ 1
AF80 ... AF96	3	0	1	1	4 max.	–	or 1	or 1	–	–	–	+ 1
AF09 ... AF96	3	0	2	2	–	–	–	–	–	+	1	–
AF40 ... AF96	3	0	2	2	–	–	–	–	–	+	1	+ 1

Overload relays fitting details (1)

Contactor types	Thermal overload relays	Electronic overload relays
AF09 ... AF38	TF42 (0.10...38 A)	EF19 (0.10...19 A)
AF26 ... AF38	TF42 (0.10...38 A)	EF45 (9...45 A)
AF40 ... AF65	TF65 (22...67 A)	EF65 (20...70 A)
AF80, AF96	TF96 (40...96 A)	EF96 (36...100 A)

The addition of an overload relay on the contactor does not prevent fitting of many other accessories as shown above.

(1) Direct mounting - No kit required.

AF09 ... AF96 2-stack 3-pole contactors

Main accessories



CAL4-11




VM4




BEA16-4



TEF4-ON



BER16-4



BEY16-4

Ordering Details (1)

For contactors	Auxiliary contacts	Type	Order code	Pkg qty	Weight (1 pce)
	 				kg

Side-mounted instantaneous auxiliary contact blocks

AF09 ... AF96	1 1	- -	CAL4-11	1SBN010120R1011	1	0.040
	1 1	- -	CAL4-11-T	1SBN010120T1011	10	0.040

Mechanical interlock unit

AF09 ... AF38	VM4	1SBN030105T1000	10	0.005
AF40 ... AF96	VM96-4	1SBN033405T1000	10	0.006

Note: VM4 and VM96-4 include 2 fixing clips (BB4) to maintain together both contactors.

For contactors	Time delay range selected by switch	Delay type	Auxiliary contacts	Type	Order code	Pkg qty	Weight (1 pce)
							kg

Electronic timers

AF40 ... AF96-30-11	0.1...1 s	ON-delay	1 1	TEF4-ON	1SBN020112R1000	1	0.065
	1...10 s	OFF-delay	1 1	TEF4-OFF	1SBN020114R1000	1	0.065
	10...100 s						

Note: Rated control circuit voltage Uc 24...240 V 50/60 Hz or DC.

Connecting links with manual motor starters

AF09 ... AF16	with	MS116-0.16 ... MS116-25, MS132-0.16 ... MS132-25	BEA16-4	1SBN081306T1000	10	0.025
AF26 ... AF38	with	MS116-0.16 ... MS116-16, MS132-0.16 ... MS132-10	BEA26-4	1SBN082306T1000	10	0.025
	with	MS116-20 ... MS116-32, MS132-12 ... MS132-32	BEA38-4	1SBN082306T2000	10	0.030
AF40 ... AF65	with	MS165-16 ... MS165-65	BEA65-4	1SBN083406R1000	1	0.090

Connection sets for reversing contactors

AF09 ... AF16	BER16-4	1SBN081311R1000	1	0.045
AF26 ... AF38	BER38-4	1SBN082311R1000	1	0.100
AF40 ... AF65	BER65-4	1SBN083411R1000	1	0.175
AF80 ... AF96	BER96-4	1SBN083911R1000	1	0.250

Connection sets for star-delta starting

AF09 ... AF16	with or without VM4	BEY16-4	1SBN081313R2000	1	0.050
AF26 ... AF38	with or without VM4	BEY38-4	1SBN082713R2000	1	0.110
AF40 ... AF65	with or without VM96-4	BEY65-4	1SBN083413R2000	1	0.200
AF80 ... AF96	with or without VM96-4	BEY96-4	1SBN083913R2000	1	0.250

(1) For more information, refer to "Accessories" section.