

Manual switch-disconnectors OT160...4000, IEC

Ordering information for side operated switch-disconnectors



OT160EV...250ES04K
OT200...250ES04K



OT630...800ES03K



OT630...800ES04



OT630...800ES04K

Side operated switch-disconnectors, base mounting, IEC

Including terminal bolt kit. In OT_K -types a black ON-OFF direct mount handle as standard. The handle is padlockable in the OFF-position.

Number of poles	Open air thermal current I _{th}	Rated operat. currents AC22A/AC23A 400...415 V	Type	Order code	Weight/unit kg
	A	A/A			
Handle has to be ordered separately					
3	200	200/160	OT160EV...S03	1SCA120563R1001	1.8
4	200	200/160	OT160EV...S04	1SCA120564R1001	2.2
3	200	200/200	OT200ES...S03	1SCA022860R0200	1.8
4	200	200/200	OT200ES...S04	1SCA022860R0540	2.2
3	250	250/250	OT250ES...S03	1SCA022860R0890	1.8
4	250	250/250	OT250ES...S04	1SCA022860R1010	2.2
3	315	315/315	OT315ES...S03	1SCA022860R1270	3.4
4	315	315/315	OT315ES...S04	1SCA022860R1510	4.0
3	400	400/400	OT400ES...S03	1SCA022860R1780	3.4
4	400	400/400	OT400ES...S04	1SCA022860R1940	4.0
3	630	630/630	OT630ES...S03	1SCA022860R2240	7.0
4	630	630/630	OT630ES...S04	1SCA022860R2410	8.2
3	800	800/800	OT800ES...S03	1SCA022860R2670	7.0
4	800	800/800	OT800ES...S04	1SCA022860R2830	8.2
Direct mount handle included					
3	200	200/160	OT160EV...S03K	1SCA120570R1001	1.9
4	200	200/160	OT160EV...S04K	1SCA120565R1001	2.3
3	200	200/200	OT200ES...S03K	1SCA022860R0620	1.9
4	200	200/200	OT200ES...S04K	1SCA022860R0710	2.3
3	250	250/250	OT250ES...S03K	1SCA022860R0970	1.9
4	250	250/250	OT250ES...S04K	1SCA022860R1190	2.3
3	315	315/315	OT315ES...S03K	1SCA022860R1350	3.5
4	315	315/315	OT315ES...S04K	1SCA022860R1600	4.1
3	400	400/400	OT400ES...S03K	1SCA022860R1860	3.5
4	400	400/400	OT400ES...S04K	1SCA022860R2080	4.1
3	630	630/630	OT630ES...S03K	1SCA022860R2320	7.0
4	630	630/630	OT630ES...S04K	1SCA022860R2590	8.4
3	800	800/800	OT800ES...S03K	1SCA022860R2750	7.2
4	800	800/800	OT800ES...S04K	1SCA022860R2910	8.4

Terminal bolt kits included as standard

Suitable for switches	Terminal bolt kit
OT160EV...250	M8x25
OT315...400	M10x30
OT630...800	M12x40