

General Information

Extended Product Type:	OHG65J6
Product ID:	1SCA022380R9740
EAN:	6417019124124
Catalog Description:	OHG65J6 Handle
Long Description:	Handle

Categories

Products » Low Voltage Products and Systems » Switches » Switch Disconnectors Accessories

Ordering

EAN:	6417019124124
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85381000

Dimensions

Product Net Width:	98 mm
Product Net Height:	66 mm
Product Net Length:	100 mm
Product Net Depth:	45 mm
Product Net Weight:	0.120 kg

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	70 mm
Package Level 1 Height:	50 mm
Package Level 1 Length:	100 mm
Package Level 1 Gross Weight:	0.120 kg
Package Level 1 EAN:	6417019124124

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-07-01
--------------	--

Additional Information

Color:	Grey
Degree of Protection:	IP65
Handle Length:	65 mm
Handle Type:	Pistol
Order Multiple:	10 piece
Product Main Type:	OHG
Product Name:	Handle
Product Type:	OHG
Special Functions:	J6
Suitable For:	OT63...250
Suitable for Product Class:	Switch disconnectors

Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	1SCC301020C0201
RoHS Information:	1SCC390010D0201

Classifications

ETIM 5:	EC000229 - Handle for power circuit breaker
Object Classification Code:	N/A

