

### General Information

Extended Product Type:	OHG80J6
Product ID:	1SCA022381R0320
EAN:	6417019124186
Catalog Description:	OHG80J6 Handle
Long Description:	Handle

### Categories

Products » Low Voltage Products and Systems » Switches » Switch Disconnectors Accessories

### Ordering

EAN:	6417019124186
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85381000

### Dimensions

Product Net Width:	113 mm
Product Net Height:	66 mm
Product Net Length:	115 mm
Product Net Depth:	45 mm
Product Net Weight:	0.120 kg

### Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	70 mm
Package Level 1 Height:	50 mm
Package Level 1 Length:	115 mm
Package Level 1 Gross Weight:	0.120 kg
Package Level 1 EAN:	6417019124186

### Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-07-01
--------------	--

### Additional Information

Color:	Grey
Degree of Protection:	IP65
Handle Length:	80 mm
Handle Type:	Pistol
Order Multiple:	10 piece
Product Main Type:	OHG
Product Name:	Handle
Product Type:	OHG
Special Functions:	J6
Suitable For:	OT160...250_
Suitable for Product Class:	Switch disconnectors

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	1SCC301020C0201
RoHS Information:	1SCC390005D0202

### Classifications

ETIM 5:	EC000229 - Handle for power circuit breaker
Object Classification Code:	N/A

