

### General Information

Extended Product Type:	OHY175J10
Product ID:	1SCA022536R2570
EAN:	6417019169866
Catalog Description:	No Description Available
Long Description:	Pistol type plastic handle, IP65 (NEMA1, 12, 3R, 12) padlockable with 3 padlocks in OFF position, door interlock in ON position

### Categories

Products » Low Voltage Products and Systems » Switches » Switch Disconnectors Accessories

### Ordering

EAN:	6417019169866
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85389099

### Dimensions

Product Net Width:	208 mm
Product Net Height:	66 mm
Product Net Depth:	45 mm

### Container Information

Package Level 1 Units:	1 piece
Package Level 1 Gross Weight:	0,18 kg
Package Level 1 EAN:	6417019169866

### Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2009 Q4
--------------	---

### Additional Information

Color:	Red-Yellow
Degree of Protection:	IP65
Handle Length:	175 mm
Handle Type:	Pistol
Order Multiple:	1 piece
Product Main Type:	OHY175
Product Name:	Handle
Product Type:	OHY
Special Functions:	J10
Suitable For:	MCCB
Suitable for Product Class:	Switches

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	1SCC301020C0201
------------------------------------	-----------------

### Classifications

ETIM 5:	EC000229 - Handle for power circuit breaker
Object Classification Code:	N/A



