

### General Information

|                        |  |
|------------------------|--|
| Extended Product Type: | OHY274J12  |
| Product ID:            | 1SCA115919R1001  |
| EAN:                   | 6417019481906  |
| Catalog Description:   | Handle OHY274J12   |
| Long Description:      | IP65, NEMA 1, 3R, 12, padlockable with three padlocks in OFF-position, door interlock in ON- position. Screw fixing from the back side of the handle. No screws on the front ensures double insulation. The type and the ordering numbers are for one piece, red-yellow. |

### Categories

Products » Low Voltage Products and Systems » Switches » Switch Disconnectors Accessories

### Ordering

|                         |               |
|-------------------------|---------------|
| EAN:                    | 6417019481906 |
| Minimum Order Quantity: | 1 piece       |
| Customs Tariff Number:  | 85389099      |

### Dimensions

|                     |          |
|---------------------|----------|
| Product Net Width:  | 308 mm   |
| Product Net Height: | 69,4 mm  |
| Product Net Depth:  | 70 mm    |
| Product Net Weight: | 0.515 kg |

### Container Information

|                               |               |
|-------------------------------|---------------|
| Package Level 1 Units:        | 25 piece      |
| Package Level 1 Width:        | 274 mm        |
| Package Level 1 Height:       | 66 mm         |
| Package Level 1 Length:       | 80 mm         |
| Package Level 1 Gross Weight: | 0.54 kg       |
| Package Level 1 EAN:          | 6417019481906 |

### Environmental

|              |   |
|--------------|---|
| RoHS Status: | Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2009 Q4 |
|--------------|---|

### Additional Information

|                             |                               |
|-----------------------------|-------------------------------|
| Color:                      | Red-Yellow                    |
| Degree of Protection:       | IP65                          |
| Handle Length:              | 274 mm                        |
| Handle Type:                | Pistol                        |
| IIT Publishing Status:      | Level 0 - Information enabled |
| Order Multiple:             | 1 piece                       |
| Product Main Type:          | OHY274                        |
| Product Name:               | HANDLE                        |
| Product Type:               | OHY                           |
| Special Functions:          | J12                           |
| Suitable For:               | OS1250 & OT1000-3200          |
| Suitable for Product Class: | Switches                      |

### Certificates and Declarations (Document Number)

|                                    |                 |
|------------------------------------|-----------------|
| Data Sheet, Technical Information: | 1SCC301020C0201 |
| Declaration of Conformity - CE:    | 1SCC390030D0203 |

### Classifications

|                             |   |
|-----------------------------|---|
| ETIM 5:                     | EC000229 - Handle for power circuit breaker |
| Object Classification Code: | N/A   |

