

General Information

Extended Product Type:	OHYS2AJR
Product ID:	1SCA105309R1001
EAN:	6417019412375
Catalog Description:	Handle OHYS2AJR
Long Description:	IP65, NEMA 1, 3R, 12, padlockable with three padlocks in OFF-position, door interlock in ON- position. Screw fixing from the back side of the handle. No screws on the front ensures double insulation. The type and the ordering numbers are for one piece, red-yellow.

Categories

Products » Low Voltage Products and Systems » Switches » Disconnect Switches Accessories

Ordering

EAN:	6417019412375
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85389099

Dimensions

Product Net Width:	66 mm
Product Net Height:	66 mm
Product Net Depth:	48 mm
Product Net Weight:	0.072 kg

Container Information

Package Level 1 Units:	120 piece
Package Level 1 Width:	50 mm
Package Level 1 Height:	50 mm
Package Level 1 Length:	50 mm
Package Level 1 Gross Weight:	0.072 kg
Package Level 1 EAN:	6417019412375

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2009 Q4
--------------	---

Additional Information

Color:	Red-Yellow
Degree of Protection:	IP65
Handle Type:	Selector
IIT Publishing Status:	Level 0 - Information enabled
Order Multiple:	1 piece
Product Main Type:	OHYS2
Product Name:	HANDLE
Product Type:	OHYS
Suitable For:	OT16-125 & OTDC16-32
Suitable for Product Class:	Switch disconnectors

Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	1SCC301020C0201
Declaration of Conformity - CE:	1SCC390030D0203

Classifications

ETIM 5:	EC000229 - Handle for power circuit breaker
Object Classification Code:	N/A

