

### General Information

Extended Product Type:	OHYS3AH
Product ID:	1SCA105325R1001
EAN:	6417019412450
Catalog Description:	OHYS3AH Handle
Long Description:	Selector type handle. Indication I-O and ON-OFF, for shaft diameter 6 mm, door drilling 22.5 mm. IP 54 handles, padlockable with one padlock with bail diameter 5...6.3 mm, NEMA 1, red-yellow, OT16...125F

### Categories

Products » Low Voltage Products and Systems » Switches » Disconnect Switches Accessories

### Ordering

EAN:	6417019412450
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85381000

### Dimensions

Product Net Width:	48 mm
Product Net Height:	48 mm
Product Net Depth:	41 mm
Product Net Weight:	0.1 kg

### Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	48 mm
Package Level 1 Height:	41 mm
Package Level 1 Length:	48 mm
Package Level 1 Gross Weight:	0.1 kg
Package Level 1 EAN:	6417019412450

### Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-07-01
--------------	--

### Additional Information

Color:	Red-Yellow
Degree of Protection:	IP54
Handle Type:	Selector
IIT Publishing Status:	Level 0 - Information enabled
Order Multiple:	10 piece
Product Main Type:	OHYS3AH
Product Name:	Handle
Product Type:	OHYS
Suitable For:	OT16 ... 125F
Suitable for Product Class:	Switch disconnectors

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	<a href="#">1SCC301020C0201</a>
RoHS Information:	<a href="#">1SCC390005D0202</a>

### Classifications

ETIM 5:	EC000229 - Handle for power circuit breaker
Object Classification Code:	N/A

