

General Information

Extended Product Type:	OHB274J12E011
Product ID:	1SCA122306R1001
EAN:	6417019532547
Catalog Description:	Handle OHB274J12E011
Long Description:	Padlockable with 3 padlocks in the OFF-position, door interlock in the ON-position. Units/type = 1 pcs. Screw fixing from the back side of the handle, no screws on the front, ensures double insulation, black.

Categories

Products » Low Voltage Products and Systems » Switches » Switch Disconnectors Accessories

Ordering

EAN:	6417019532547
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85389099

Dimensions

Product Net Width:	308 mm
Product Net Height:	69,4 mm
Product Net Depth:	70 mm
Product Net Weight:	0.515 kg

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	310 mm
Package Level 1 Height:	70 mm
Package Level 1 Length:	50 mm
Package Level 1 Gross Weight:	0.54 kg
Package Level 1 EAN:	6417019532547

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2009 Q4
--------------	---

Additional Information

Color:	Black
Degree of Protection:	IP65
Handle Length:	274 mm
Handle Type:	Pistol
IIT Publishing Status:	Level 0 - Information enabled
Order Multiple:	1 piece
Product Main Type:	OHB274
Product Name:	HANDLE
Product Type:	OHB
Special Functions:	J12E011
Suitable For:	OT1000-3200C
Suitable for Product Class:	Switches

Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	1SCC303003C0201
Declaration of Conformity - CE:	1SCC390030D0203

Classifications

ETIM 5:	EC000229 - Handle for power circuit breaker
Object Classification Code:	N/A

