

### General Information

Extended Product Type:	OHB95J12T
Product ID:	1SCA022736R1750
EAN:	6417019238470
Catalog Description:	Handle OHB95J12T
Long Description:	Padlockable with 3 padlocks in the OFF-position, door interlock in the ON-position. Units/type = 1 pcs. Screw fixing from the back side of the handle, no screws on the front, ensures double insulation, black.

### Categories

Products » Low Voltage Products and Systems » Switches » Switch Disconnectors Accessories

### Ordering

EAN:	6417019238470
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85389099

### Dimensions

Product Net Width:	128 mm
Product Net Height:	66 mm
Product Net Depth:	45 mm
Product Net Weight:	0.01 kg

### Container Information

Package Level 1 Units:	90 piece
Package Level 1 Width:	95 mm
Package Level 1 Height:	66 mm
Package Level 1 Length:	80 mm
Package Level 1 Gross Weight:	0.12 kg
Package Level 1 EAN:	6417019238470

### Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2009 Q4
--------------	---

### Additional Information

Color:	Black
Degree of Protection:	IP65
Handle Length:	95 mm
Handle Type:	Pistol
IIT Publishing Status:	Level 0 - Information enabled
Order Multiple:	1 piece
Product Main Type:	OHB95
Product Name:	HANDLE
Product Type:	OHB
Special Functions:	J12T
Suitable For:	OS315-400 & OT315-400
Suitable for Product Class:	Switches

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	1SCC301020C0201
Declaration of Conformity - CE:	1SCC390030D0203

### Classifications

ETIM 5:	EC000229 - Handle for power circuit breaker
Object Classification Code:	N/A

