

General Information

Extended Product Type:	OHBS10AJ
Product ID:	1SCA105203R1001
EAN:	6417019410401
Catalog Description:	Handle OHBS10AJ
Long Description:	For shaft diameter 6 mm, door drilling 22.5 mm. Indication I-O and ON-OFF. IP65 handles, NEMA 1, 3R, 7

Categories

Products » Low Voltage Products and Systems » Switches » Switch Disconnectors Accessories

Ordering

EAN:	6417019410401
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85389099

Dimensions

Product Net Width:	66 mm
Product Net Height:	66 mm
Product Net Depth:	48 mm
Product Net Weight:	0.058 kg

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	66 mm
Package Level 1 Height:	66 mm
Package Level 1 Length:	48 mm
Package Level 1 Gross Weight:	0.058 kg
Package Level 1 EAN:	6417019410401

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2009 Q4
--------------	---

Additional Information

Color:	Black
Degree of Protection:	IP54
Handle Type:	Selector
IIT Publishing Status:	Level 0 - Information enabled
Order Multiple:	1 piece
Product Main Type:	OHBS10
Product Name:	HANDLE
Product Type:	OHBS
Suitable for Product Class:	Switch disconnectors

Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	1SCC301020C0201
Declaration of Conformity - CE:	1SCC390030D0203

Classifications

ETIM 5:	EC000229 - Handle for power circuit breaker
Object Classification Code:	N/A



