

### General Information

Extended Product Type:	OHBS11
Product ID:	1SCA109092R1001
EAN:	6417019424699
Catalog Description:	Handle OHBS11
Long Description:	For shaft diameter 6 mm, door drilling 22.5 mm. Indication I-O and ON-OFF. IP65 handles, NEMA 1, 3R, 9

### Categories

Products » Low Voltage Products and Systems » Switches » Disconnect Switches Accessories

### Ordering

EAN:	6417019424699
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85389099

### Dimensions

Product Net Width:	20 mm
Product Net Height:	20 mm
Product Net Depth:	20 mm
Product Net Weight:	0.01 kg

### Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	20 mm
Package Level 1 Height:	20 mm
Package Level 1 Length:	20 mm
Package Level 1 Gross Weight:	0.014 kg
Package Level 1 EAN:	6417019424699

### Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2009 Q4
--------------	---

### Additional Information

Color:	Black
Handle Type:	Knob
IIT Publishing Status:	Level 0 - Information enabled
Order Multiple:	10 piece
Product Main Type:	OHBS11
Product Name:	HANDLE
Product Type:	OHBS
Suitable for Product Class:	Switch disconnectors

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	<a href="#">1SCC301020C0201</a>
Declaration of Conformity - CE:	<a href="#">1SCC390030D0203</a>

### Classifications

ETIM 5:	EC000229 - Handle for power circuit breaker
Object Classification Code:	N/A

