

General Information

Extended Product Type:	OHBS2RN
Product ID:	1SCA116075R1001
EAN:	6417019602318
Catalog Description:	Handle OHBS2RN
Long Description:	Screw mounting, hole distance 36 mm. Padlockable with one padlock, IP54, NEMA 1

Categories

Products » Low Voltage Products and Systems » Switches » Switch Disconnectors Accessories

Ordering

EAN:	6417019602318
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85389099

Dimensions

Product Net Width:	66 mm
Product Net Height:	66 mm
Product Net Depth:	44 mm
Product Net Weight:	0.072 kg

Container Information

Package Level 1 Units:	150 piece
Package Level 1 Width:	50 mm
Package Level 1 Height:	50 mm
Package Level 1 Length:	50 mm
Package Level 1 Gross Weight:	0.072 kg
Package Level 1 EAN:	6417019602318

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2009 Q4
--------------	---------------------------------------------------------------------------------------

Additional Information

Color:	Black
Degree of Protection:	IP65
Handle Type:	Selector
IIT Publishing Status:	Level 0 - Information enabled
Order Multiple:	1 piece
Product Main Type:	OHBS2
Product Name:	HANDLE
Product Type:	OHBS
Suitable For:	OT16-125 & OTDC16-32
Suitable for Product Class:	Switch disconnectors

Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	1SCC301020C0201
Declaration of Conformity - CE:	1SCC390030D0203

Classifications

ETIM 5:	EC000229 - Handle for power circuit breaker
Object Classification Code:	N/A

