

### General Information

Extended Product Type:	OHB145J12E20
Product ID:	1SCA022399R8450
EAN:	6417019135762
Catalog Description:	OHB145J12E20 Handle
Long Description:	Black, I-O and ON-OFF indication, padlockable with 3 padlocks in O- and I-position, door interlock in I-position, defeatable, IP 65.

### Categories

Products » Low Voltage Products and Systems » Switches » Switch Disconnectors Accessories
Products » Low Voltage Products and Systems » Switches » Switch Fuses Accessories » Accessories for Switch Fuses

### Ordering

EAN:	6417019135762
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85381000

### Dimensions

Product Net Width:	178 mm
Product Net Height:	66 mm
Product Net Length:	180 mm
Product Net Depth:	45 mm
Product Net Weight:	0.17 kg

### Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	70 mm
Package Level 1 Height:	50 mm
Package Level 1 Length:	180 mm
Package Level 1 Gross Weight:	0.17 kg
Package Level 1 EAN:	6417019135762

### Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-07-01
--------------	--

### Additional Information

Color:	Black
Degree of Protection:	IP65
Handle Length:	145 mm
Handle Type:	Pistol
Order Multiple:	1 piece
Product Main Type:	OHB145J12E20
Product Name:	Handle
Product Type:	OHB
Special Functions:	J12E20
Suitable For:	OT90_...315_
Suitable for Product Class:	Switch disconnectors

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	<a href="#">1SCC301020C0201</a>
RoHS Information:	<a href="#">1SCC390010D0201</a>

### Classifications

ETIM 5:	EC000229 - Handle for power circuit breaker
Object Classification Code:	N/A

