

### Front operated switch-disconnectors

Types OT 16...125 include protected terminal clamps, IP 20.  
The type and the ordering numbers are for one piece.

| Number of poles | I <sub>th</sub> (open) [A] | Cable cross section [mm <sup>2</sup> ] | Rated operat. currents AC22A/AC23A 400V [A/A] | Type                  | Order number    | Delivery batch [pcs] | Weight/unit [kg] |
|-----------------|----------------------------|--|---|-----------------------|-----------------|----------------------|------------------|
| 3               | 25                         | 0.75...10                              | 16 / 16                                       | OT16E3                | 1SCA022283R8470 | 10                   | 0.11             |
| 4               | 25                         | 0.75...10                              | 16 / 16                                       | OT16E4                | 1SCA022352R7170 | 10                   | 0.14             |
| 3               | 32                         | 0.75...10                              | 25 / 20                                       | OT25E3                | 1SCA022283R8630 | 10                   | 0.11             |
| 4               | 32                         | 0.75...10                              | 25 / 20                                       | OT25E4                | 1SCA022352R7330 | 10                   | 0.14             |
| 3               | 40                         | 0.75...10                              | 40 / 23                                       | OT32E3                | 1SCA022283R9010 | 10                   | 0.11             |
| 4               | 40                         | 0.75...10                              | 40 / 23                                       | OT32E4                | 1SCA022352R7500 | 10                   | 0.14             |
| 3               | 63                         | 1.5...35                               | 63 / 45                                       | OT45E3                | 1SCA022352R6950 | 10                   | 0.27             |
| 4               | 63                         | 1.5...35                               | 63 / 45                                       | OT45E4                | 1SCA022352R7680 | 10                   | 0.30             |
| 3               | 80                         | 1.5...35                               | 80 / 75                                       | OT63E3                | 1SCA022352R7090 | 10                   | 0.27             |
| 4               | 80                         | 1.5...35                               | 80 / 75                                       | OT63E4                | 1SCA022352R7760 | 10                   | 0.30             |
| 3               | 80                         | 2.5...50                               | 80 / 55                                       | OT80E3                | 1SCA022353R7210 | 10                   | 0.32             |
| 4               | 80                         | 2.5...50                               | 80 / 55                                       | OT80E4                | 1SCA022369R2960 | 10                   | 0.40             |
| 3               | 115                        | 10...70                                | 100 / 80                                      | OT100E3               | 1SCA022398R4400 | 10                   | 0.36             |
| 4               | 115                        | 10...70                                | 100 / 80                                      | OT100E4               | 1SCA022398R4580 | 10                   | 0.50             |
| 3               | 125                        | 10...70                                | 125 / 90                                      | OT125E3               | 1SCA022353R7480 | 10                   | 0.36             |
| 4               | 125                        | 10...70                                | 125 / 90                                      | OT125E4               | 1SCA022373R1880 | 10                   | 0.50             |
| 3               | 200                        |  | 200 <sup>1)</sup> /135                        | OT160E3 <sup>2)</sup> | 1SCA022257R5950 | 1                    | 1.2              |
| 4               | 200                        |  | 200 <sup>1)</sup> /135                        | OT160E4 <sup>2)</sup> | 1SCA022259R8060 | 1                    | 1.4              |
| 3               | 200                        |  | 200 <sup>1)</sup> /135                        | OT160E3-2             | 1SCA022297R4060 | 1                    | 1.0              |

### Shafts and handles included as standard

| Suitable for switches | Included shaft | Included handle |
|-----------------------|----------------|-----------------|
| OT160E3, _E4          | OXF6X210       | OHB65J6         |

### Front operated, 6- and 8-pole switch-disconnectors

Including protected terminal clamps, IP 20.

| Suitable shaft dia. [mm] | I <sub>th</sub> (open) [A] | Cable cross section [mm <sup>2</sup> ] | Operational currents AC22/AC23 400V [A/A] | Type    | Order number    | Units/type [pcs] | Weight/unit [kg] |
|--------------------------|----------------------------|--|---|---------|-----------------|------------------|------------------|
| <b>6-pole</b>            |                            |  |   |         |                 |                  |                  |
| 5                        | 25                         | 0.75...10                              | 16/16                                     | OT16E6  | 1SCA022551R4420 | 1                | 0.25             |
| 5                        | 32                         | 0.75...10                              | 25/20                                     | OT25E6  | 1SCA022551R5230 | 1                | 0.25             |
| 5                        | 40                         | 0.75...10                              | 40/23                                     | OT32E6  | 1SCA022551R2720 | 1                | 0.25             |
| 6                        | 63                         | 1.5...35                               | 63/45                                     | OT45E6  | 1SCA022551R3610 | 1                | 0.61             |
| 6                        | 80                         | 1.5...35                               | 80/75                                     | OT63E6  | 1SCA022551R6040 | 1                | 0.61             |
| 6                        | 80                         | 2.5...50                               | 80/55                                     | OT80E6  | 1SCA022551R6800 | 1                | 0.71             |
| 6                        | 115                        | 10...70                                | 100/80                                    | OT100E6 | 1SCA022551R7610 | 1                | 0.81             |
| 6                        | 125                        | 10...70                                | 125/90                                    | OT125E6 | 1SCA022551R8410 | 1                | 0.81             |
| <b>8-pole</b>            |                            |  |   |         |                 |                  |                  |
| 5                        | 25                         | 0.75...10                              | 16/16                                     | OT16E8  | 1SCA022551R4510 | 1                | 0.31             |
| 5                        | 32                         | 0.75...10                              | 25/20                                     | OT25E8  | 1SCA022551R5310 | 1                | 0.31             |
| 5                        | 40                         | 0.75...10                              | 40/23                                     | OT32E8  | 1SCA022551R2990 | 1                | 0.31             |
| 6                        | 63                         | 1.5...35                               | 63/45                                     | OT45E8  | 1SCA022551R3700 | 1                | 0.67             |
| 6                        | 80                         | 1.5...35                               | 80/75                                     | OT63E8  | 1SCA022551R6120 | 1                | 0.67             |
| 6                        | 80                         | 2.5...50                               | 80/55                                     | OT80E8  | 1SCA022551R6980 | 1                | 0.87             |
| 6                        | 115                        | 10...70                                | 100/80                                    | OT100E8 | 1SCA022551R7790 | 1                | 1.1              |
| 6                        | 125                        | 10...70                                | 125/90                                    | OT125E8 | 1SCA022551R8500 | 1                | 1.1              |

<sup>1)</sup> 200A/min. 95 mm<sup>2</sup>, use busbar connections OEZXX6/13 or OZXT2

<sup>2)</sup> Handle and shaft included