

RCCBs

F 200 series AC  type



F204



F204 125 A

Number of poles	Rated residual current I Δ n mA	Rated current In A	Bbn 8012542 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
				Type code	Order code			
4	30	25	781202	F204 AC-25/0.03	2CSF204001R1250		0.375	1/3
		40	781301	F204 AC-40/0.03	2CSF204001R1400		0.375	1/3
		63	781400	F204 AC-63/0.03	2CSF204001R1630		0.375	1/3
		80	916604	F204 AC-80/0.03	2CSF204001R1800		0.405	1/3
		100	916703	F204 AC-100/0.03	2CSF204001R1900		0.405	1/3
		125	941507	F204 AC-125/0.03	2CSF204001R1950		0.500	1
		100	25	25	781509	F204 AC-25/0.1	2CSF204001R2250	
40	781608			F204 AC-40/0.1	2CSF204001R2400		0.375	1/3
63	781707			F204 AC-63/0.1	2CSF204001R2630		0.375	1/3
80	916802			F204 AC-80/0.1	2CSF204001R2800		0.405	1/3
100	916901			F204 AC-100/0.1	2CSF204001R2900		0.405	1/3
125	941606			F204 AC-125/0.1	2CSF204001R2950		0.500	1
300	25	25	781806	F204 AC-25/0.3	2CSF204001R3250		0.375	1/3
		40	781905	F204 AC-40/0.3	2CSF204001R3400		0.375	1/3
		63	782001	F204 AC-63/0.3	2CSF204001R3630		0.375	1/3
		80	917007	F204 AC-80/0.3	2CSF204001R3800		0.405	1/3
		100	917106	F204 AC-100/0.3	2CSF204001R3900		0.405	1/3
		125	941705	F204 AC-125/0.3	2CSF204001R3950		0.500	1
500	25	25	782100	F204 AC-25/0.5	2CSF204001R4250		0.375	1/3
		40	782209	F204 AC-40/0.5	2CSF204001R4400		0.375	1/3
		63	782308	F204 AC-63/0.5	2CSF204001R4630		0.375	1/3
		80	917205	F204 AC-80/0.5	2CSF204001R4800		0.405	1/3
		100	917304	F204 AC-100/0.5	2CSF204001R4900		0.405	1/3
		125	941804	F204 AC-125/0.5	2CSF204001R4950		0.500	1