





4 pole 16A – 3150A

Disconnect
switches
Non-fusible
Enclosed

4 Pole, 600V, 16A – 3150A

| UL general purpose amp rating | | NEMA Enclosure type | | | | |
|----------------------------------|---|---------------------|----------------|----------------|----------------|--------------|
| | | 1 | 3R | 4 | 4X Stainless | |
| | | Catalog number | Catalog number | Catalog number | Catalog number | |
| UL508 |  | 16 | NF161-4PB6C | NF163-4PB6C | NF164-4PB6A | NF16X-4PB6C |
| | | 25 | NF251-4PB6C | NF253-4PB6C | NF254-4PB6A | NF25X-4PB6C |
| | | 40 | NF321-4PB6C | NF323-4PB6C | NF324-4PB6A | NF32X-4PB6C |
| UL98 |  | 60 | NF451-4PB6B | NF453-4PB6B | NF454-4PB6B | NF45X-4PB6B |
| | | 80 | NF631-4PB6A | NF633-4PB6A | NF634-4PB6A | NF63X-4PB6A |
| | | 30 | NF301-4PB6B | NF303-4PB6B | NF304-4PB6B | NF30X-4PB6B |
| | | 60 | NF601-4PB6B | NF603-4PB6B | NF604-4PB6B | NF60X-4PB6B |
| | | 100 | NF1001-4PB6B | NF1003-4PB6B | NF1004-4PB6B | NF100X-4PB6B |
| | | 125 | NF1251-4PB6A | NF1253-4PB6A | NF1254-4PB6A | NF125X-4PB8A |
| | | 200 | NF2001-4PB8B | NF2003-4PB8B | NF2004-4PB8B | NF200X-4PB8B |
| | | 400 | NF4001-4PB4B | NF4003-4PB4B | NF4004-4PB4B | NF400X-4PB4B |
| | | 600 | NF6001-4PB7B | NF6003-4PB7B | NF6004-4PB7B | NF600X-4PB7B |
| | | 800 | NF8001-4PB4A | NF8003-4PB4A | NF8004-4PB4A | NF800X-4PB4A |
| 1200 | NF12001-4PB4A | NF12003-4PB4A | NF12004-4PB4A | NF1200X-4PB4A | | |
| 1600 | NF16001-4P8A | NF16003-4P8A | NF16004-4P8A | NF1600X-4P8A | | |
| 2000 | NF20001-4P8A | NF20003-4P8A | NF20004-4P8A | NF2000X-4P8A | | |
| 3150 ① | NF31501-4P8A | NF31503-4P8A | NF31504-4P8A | NF3150X-4P8A | | |

4 Pole, 600V, 16A – 3150A

| UL general purpose amp rating | | NEMA Enclosure type | | | |
|----------------------------------|---|---------------------|----------------|----------------|-----------|
| | | 4X Plastic | 12 | 7 & 9 | |
| | | Catalog number | Catalog number | Catalog number | |
| UL508 |  | 16 | NF16P-4PB6A | NF162-4PB6C | NF167-4P |
| | | 25 | NF25P-4PB6A | NF252-4PB6C | NF257-4P |
| | | 40 | NF32P-4PB6A | NF322-4PB6C | NF327-4P |
| UL98 |  | 60 | NF45P-4PB6B | NF452-4PB6B | NF457-4P |
| | | 80 | NF63P-4PB6A | NF632-4PB6A | NF637-4P |
| | | 30 | NF30P-4PB6B | NF302-4PB6B | NF307-4P |
| | | 60 | NF60P-4PB6B | NF602-4PB6B | NF607-4P |
| | | 100 | NF100P-4PB6B | NF1002-4PB6B | NF1007-4P |
| | | 125 | NF125P-4PB8A | NF1252-4PB6A | — |
| | | 200 | NF200P-4PB8B | NF2002-4PB8B | — |
| | | 400 | NF400P-4PB4B | NF4002-4PB4B | — |
| | | 600 | NF600P-4PB7B | NF6002-4PB7B | — |
| | | 800 | NF800P-4PB4A | NF8002-4PB4A | — |
| 1200 | NF1200P-4PB4A | NF12002-4PB4A | — | | |
| 1600 | — | NF16002-4P8A | — | | |
| 2000 | — | NF20002-4P8A | — | | |
| 3150 | — | NF31502-4P8A | — | | |

① IEC rated only.