

# MC812PA terminal block markers

## Pre-printed marker card for vertical terminal block assembly



MC812PA



8 mm 0.315 in spacing

### Ordering details

Description	Number of markers per card	Color	Type	Order code	Pkg card	Weight (1 pce)
← Continuation of previous page						
W (x100)	100	White	MC812PA	1SNK166232R0000	1	14.00
X (x100)	100	White	MC812PA	1SNK166242R0000	1	14.00
Y (x100)	100	White	MC812PA	1SNK166252R0000	1	14.00
Z (x100)	100	White	MC812PA	1SNK166262R0000	1	14.00
0 (x100)	100	White	MC812PA	1SNK167002R0000	1	14.00
1 (x100)	100	White	MC812PA	1SNK167012R0000	1	14.00
2 (x100)	100	White	MC812PA	1SNK167022R0000	1	14.00
3 (x100)	100	White	MC812PA	1SNK167032R0000	1	14.00
4 (x100)	100	White	MC812PA	1SNK167042R0000	1	14.00
5 (x100)	100	White	MC812PA	1SNK167052R0000	1	14.00
6 (x100)	100	White	MC812PA	1SNK167062R0000	1	14.00
7 (x100)	100	White	MC812PA	1SNK167072R0000	1	14.00
8 (x100)	100	White	MC812PA	1SNK167082R0000	1	14.00
9 (x100)	100	White	MC812PA	1SNK167092R0000	1	14.00
+ (x100)	100	White	MC812PA	1SNK168002R0000	1	14.00
- (x100)	100	White	MC812PA	1SNK168012R0000	1	14.00
~ (x100)	100	White	MC812PA	1SNK168022R0000	1	14.00
= (x100)	100	White	MC812PA	1SNK168032R0000	1	14.00
± (x100)	100	White	MC812PA	1SNK168042R0000	1	14.00
L1 (x100)	100	White	MC812PA	1SNK168052R0000	1	14.00
L2 (x100)	100	White	MC812PA	1SNK168062R0000	1	14.00
L3 (x100)	100	White	MC812PA	1SNK168072R0000	1	14.00
PE (x100)	100	White	MC812PA	1SNK168092R0000	1	14.00
U1 (x100)	100	White	MC812PA	1SNK168102R0000	1	14.00
U2 (x100)	100	White	MC812PA	1SNK168112R0000	1	14.00
U3 (x100)	100	White	MC812PA	1SNK168122R0000	1	14.00
V1 (x100)	100	White	MC812PA	1SNK168132R0000	1	14.00
V2 (x100)	100	White	MC812PA	1SNK168142R0000	1	14.00
V3 (x100)	100	White	MC812PA	1SNK168152R0000	1	14.00
W1 (x100)	100	White	MC812PA	1SNK168162R0000	1	14.00
W2 (x100)	100	White	MC812PA	1SNK168172R0000	1	14.00
W3 (x100)	100	White	MC812PA	1SNK168182R0000	1	14.00
+24V (x100)	100	White	MC812PA	1SNK168192R0000	1	14.00
+48V (x100)	100	White	MC812PA	1SNK168202R0000	1	14.00
-24V (x100)	100	White	MC812PA	1SNK168212R0000	1	14.00
-48V (x100)	100	White	MC812PA	1SNK168222R0000	1	14.00
L1-L2-L3-N-PE (x20)	100	White	MC812PA	1SNK169002R0000	1	14.00
U1-U2-U3-V1-V2-V3-W1-W2-W3 (x10) + U1 (x10)	100	White	MC812PA	1SNK169012R0000	1	14.00

All the technical data for UL/CSA standard and dimensions in inches are in italic.