


AF09 ... AF38 4-pole contactors

Terminal marking and positioning









2

AF09 ... AF38 contactors - AC / DC operated

Standard devices without addition of auxiliary contacts



Other possible contact combinations with auxiliary contacts added by the user



Note: Only AF.Z contactor with DC control voltage 12...20 V DC need to respect the connection polarities indicated close to the coil terminals: A1+ for the positive pole and A2- for the negative pole