



PRODUCT-DETAILS

OESAZW2

OESAZW2 Conversion kit



General Information

Extended Product Type	OESAZW2
Product ID	1SCA022078R1600
EAN	6417019017068
Catalog Description	OESAZW2 Conversion kit
Long Description	Attachment levers provided with holes, enabling different shaft distances. The combination switches can be mounted either horizontally or vertically. Two 3 or 4-pole switches needed. Including OHB145J12 operating handle

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SCC011021D0201
RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85389099
Country of Origin	Finland (FI)

Popular Downloads

Data Sheet, Technical Information	1SCC301001C0201
Instructions and Manuals	No Instructions and Manuals needed

Dimensions

Product Net Width	215 mm
Product Net Height	300 mm
Product Net Depth / Length	65 mm
Product Net Weight	0.55 kg

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	215 mm
Package Level 1 Depth / Length	300 mm
Package Level 1 Height	65 mm
Package Level 1 Gross Weight	0.8 kg
Package Level 1 EAN	6417019017068
Package Level 2 Units	1 piece
Package Level 2 Gross Weight	0.80 kg

Classifications

Object Classification Code	N/A
ETIM 8	EC002498 - Accessories/spare parts for low-voltage switch technology
ETIM 9	EC002498 - Accessories/spare parts for low-voltage switch technology
UNSPSC	39122221
IDEA Granular Category Code (IGCC)	5219 >> Switch part or accessory
eClass	V11.1 : 27371392
WEEE Category	Product Not in WEEE Scope
E-Number (Finland)	3660102
E-Number (Norway)	4337376

Categories

Low Voltage Products and Systems → Switches → Switch Disconnectors

Low Voltage Products and Systems → Switches → Switch Fuses → Accessories for Switch Fuses

