



 PRODUCT-DETAILS

CEPY1-1001

CEPY1-1001 Enclosure



General Information

Extended Product Type	CEPY1-1001
Product ID	1SFA619821R1001
EAN	7320500358108
Catalog Description	CEPY1-1001 Enclosure
Long Description	Assembled Enclosure - 40mm Mushroom Emergency Stop - Twist Release - 2NC - Horisontally mounted

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85369001
Product Main Type	CEPY1

Popular Downloads

Data Sheet, Technical Information	1SFC151007C02__
Instructions and	1SFC151011M0201

Manuals

CAD Dimensional Drawing	2CDC001079B0201
-------------------------	-----------------

Dimensions

Product Net Width	0.065 m
Product Net Depth / Length	0.079 m
Product Net Height	0.065 m
Product Net Weight	0.105 kg

Technical

Accessory Type	Enclosure
Color	Yellow/Light grey
Enclosure Type NEMA	Type1 Type12 Type13 Type3R Type4 Type4X
Housing Material	Plastic
Number of Auxiliary Contacts NC	2
Rated Operational Voltage	24 ... 300 V

Environmental

Ambient Air Temperature	Operation -25 ... +70 °C Storage -40 ... +85 °C
Degree of Protection	Front IP66 Front IP67 Front IP69K Housing IP69K Housing IP66 Housing IP67 Terminals IP20
Material	Plastic
Maximum Operating Altitude Permissible	Without Derating 2000 m

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	2CMT2022-006479
RoHS Information	2CMT2022-006498
RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
SCIP	15305cb8-64f0-4aab-8bd7-19603466d43b Sweden
Simplified SCIP	217a42d7-ce39-4183-b0b7-dce1d0ec05ad Germany 6e55909a-bff3-4c94-9204-4b1077a26b4a Poland 7d422d7e-6d6b-44a0-8e19-f61d3f90599d Czech Republic 6d056065-2239-459f-a7bc-64eaa9c0fcaa Estonia c42a3000-a895-4baf-8e1b-ba7faf4126e5 Netherlands 8c55242a-aa12-4bf8-95f6-a29b5849af6f Hungary

fedf4436-1c4a-4ac0-ae4d-e9bd9729182b Greece
a71cc46e-d091-4159-9c7b-3fdbcdc2ccfc Portugal
83e25ec7-7fc2-4172-a9ac-f82db26143c8 Bulgaria
d00876d6-7b8f-47bf-933e-e90320a8b763 Sweden
b871e057-9db4-41a4-a106-c2856c45f9b3 Poland
7b5555e0-adcb-42f6-b8c8-e11bab76de45 Belgium
591667c7-e49d-4e38-ac83-39b16d15824c Germany
a393a393-1c9a-4f54-9ca2-42551302e820 France
6780b6cf-d89a-4a20-93c9-0f98d1dfd13a Hungary
b28595ee-8963-4266-8787-d7bdb16ec6ae Spain
a8dd6f70-fa3d-42ed-83a9-0550119dd949 France
68217dec-d736-48ce-9935-3df46e8d78cc Germany
cea2cddf-74cd-4332-89c7-ceac950dd27a Finland
38fb89c7-a690-4e2a-9e34-5d2fc1720a9d Italy
31b8751c-ea17-4e4a-8c30-7e5e0b21e86e Germany
94c53e66-ee3f-472d-b8a1-7a8be7b67aab Poland
ead31c56-2bb5-4b02-9d05-319d8f0d7511 Norway
45f551db-a259-48cb-b6b7-dae953c2b2d1 Germany
702792b1-db95-405c-8a64-dca282192c38 Croatia
32e5fa22-f680-4498-a8cc-320dc3d5a211 Denmark
71dd450b-8e89-4f74-b8ff-c8e09acf5e42 Belgium

Toxic Substances Control Act - TSCA	2CMT2023-006523
WEEE Category	Product Not in WEEE Scope

Certificates and Declarations

CB Certificate	CN54150
CQC Certificate	CQC2003010305054693
cURus Certificate	UL_E496500-20171020
Declaration of Conformity - CCC	2020980305001187
Declaration of Conformity - CE	2CMT2019-005802
Declaration of Conformity - UKCA	2CMT2020-006122
DNV GL Certificate	9AKK107046A3749
EAC Certificate	EAC RU C-CN.ME77.B.00537/19

Container Information

Package Level 1 Units	bag 1 piece
Package Level 1 Width	0.1 m
Package Level 1 Depth / Length	0.1 m
Package Level 1 Height	0.078 m
Package Level 1 Gross Weight	0.138 kg
Package Level 1 EAN	7320500358108

External Classifications and Standards

eClass	V11.0 : 27371216
E-Number (Finland)	2312181
E-Number (Norway)	4373373
E-Number (Sweden)	3711610
ETIM 6	EC000225 - Control circuit devices combination in enclosure
ETIM 7	EC000225 - Control circuit devices combination in enclosure
ETIM 8	EC000225 - Control circuit devices combination in enclosure

ETIM 9	EC000225 - Control circuit devices combination in enclosure
IDEA Granular Category Code (IGCC)	4478 >> Electrical pushbutton enclosure
Object Classification Code	S
UNSPSC	39121326

Categories

Low Voltage Products and Systems → Control Products → Pilot Devices → Enclosures and Assembled Stations

