

PRODUCT-DETAILS

## CR-S024VDC1R

CR-S024VDC1R Pluggable interface relay 1c/o,  
A1-A2=24VDC, Output=6A/250VAC



### General Information

|                       |  |
|-----------------------|--|
| Extended Product Type | CR-S024VDC1R   |
| Product ID            | 1SVR405501R3010  |
| EAN                   | 4013614499128  |
| Catalog Description   | CR-S024VDC1R Pluggable interface relay 1c/o, A1-A2=24VDC, Output=6A/250VAC |
| Long Description      | CR-S024VDC1R Pluggable interface relay 1c/o, A1-A2=24VDC, Output=6A/250VAC |

### Ordering

|                        |          |
|------------------------|----------|
| Minimum Order Quantity | 10 piece |
| Customs Tariff Number  | 85364900 |

### Popular Downloads

|                                   |                 |
|-----------------------------------|-----------------|
| Data Sheet, Technical Information | 2CDC117022D0201 |
| Instructions and Manuals          | 2CDC117022D0201 |

### Dimensions

|                     |       |
|---------------------|-------|
| Product Net Width   | 5 mm  |
| Product Net Height  | 15 mm |
| Product Net Depth / | 28 mm |

## Length

|                    |          |
|--------------------|----------|
| Product Net Weight | 0.005 kg |
|--------------------|----------|

## Technical

|  |                                     |
|--|-------------------------------------|
| Function                                       | Pluggable slim interface relay CR-S |
| Sub-Function                                   | Relay with standard contacts        |
| Output   | 1 c/o (SPDT) contact                |
| Output Signal                                  | 250 V / 6 A                         |
| Rated Control Supply Voltage (U <sub>s</sub> ) | 24 V DC                             |

## Environmental

|                         |  |
|-------------------------|--|
| Ambient Air Temperature | Operation -40 ... +85 °C<br>Storage 0 ... +40 °C |
| RoHS Status             | Following EU Directive 2011/65/EU                |

## Certificates and Declarations (Document Number)

|                                |                             |
|--------------------------------|-----------------------------|
| CQC Certificate                | CQC_14002108002             |
| CSA Certificate                | CSA_262671-2785865          |
| cUR Certificate                | cUR_E244330                 |
| Declaration of Conformity - CE | No declaration needed       |
| EAC Certificate                | EAC_RU_C-DE.ME77.B.00443-19 |
| Environmental Information      | 1SAA981009-2403             |
| Instructions and Manuals       | 2CDC117022D0201             |
| RoHS Information               | 1SVD981001-4400             |
| UR Certificate                 | UR_E244330                  |
| VDE Certificate                | VDE_40039479                |

## Container Information

|                                |               |
|--------------------------------|---------------|
| Package Level 1 Units          | 10 piece      |
| Package Level 1 Width          | 300 mm        |
| Package Level 1 Height         | 23.7 mm       |
| Package Level 1 Depth / Length | 7.4 mm        |
| Package Level 1 Gross Weight   | 0.06 kg       |
| Package Level 1 EAN            | 4013614486456 |

## Classifications

|                            |                            |
|----------------------------|----------------------------|
| Object Classification Code | K                          |
| ETIM 4                     | EC001437 - Switching relay |
| ETIM 5                     | EC001437 - Switching relay |
| ETIM 6                     | EC001437 - Switching relay |
| ETIM 7                     | EC001437 - Switching relay |
| eClass                     | V11.0 : 27371601           |
| UNSPSC                     | 39122331                   |
| E-Number (Finland)         | 2712354                    |
| E-Number (Sweden)          | 4001384                    |

---

## Categories

---

Low Voltage Products and Systems → Control Products → Electronic Relays and Controls → Interface Relays and Optocouplers

