



PRODUCT-DETAILS

# MEP6-0

## MEP6-0 Enclosure



360°

### General Information

Extended Product Type	MEP6-0
Product ID	1SFA611816R1000
EAN	7320500312773
Catalog Description	MEP6-0 Enclosure
Long Description	MEP6-0 Enclosure issix seats empty grey pastic enclosure This enclosure can fit both modular and compact range. Modular range can be with the unique possibility to mount up to 5 contact blocks assigned to one operator. Degree of protection: IP66 UL/NEMAtype 1, 3R, 4, 4X, 12, 13

### Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85369001
Product Main Type	MEP6

### Popular Downloads

Data Sheet, Technical	1SFC151007C02__
-----------------------	-----------------

Information

Instructions and Manuals	1SFC151011M0201
CAD Dimensional Drawing	2CDC001079B0201

**Dimensions**

Product Net Width	0.301 m
Product Net Depth / Length	0.075 m
Product Net Height	0.061 m
Product Net Weight	0.374 kg

**Technical**

Accessory Type	Enclosure
Color	Dark grey/Light grey
Enclosure Type NEMA	Type1 Type12 Type13 Type3R Type4 Type4X
Housing Material	Plastic
Suitable For	MP1 MP2 MP3 MP4 MPM1 KP6 M2SS1 M2SS2 M2SS3 M2SS4 M2SS5 M2SS6 M3SS1 M3SS2 M3SS3 M3SS4 M3SS5 M3SS6 M3SS7 M3SS8 M3SSC1 M3SSC2 M3SSC3 M3SSC4 M3SSC5 M3SSC6 M3SSC7 M3SSC8 M2SSK1 M2SSK2 M2SSK3 M2SSK4 M3SSK1 M3SSK2 M3SSK3 MTS1 MTS2 MTS3 MJS CP1

CP2  
 CP3  
 CP4  
 CP11  
 CP12  
 CP33  
 C2SS1  
 C2SS2  
 C2SS3  
 CPM3  
 CL  
 CL2  
 CB1  
 CP6  
 P9MP  
 P9MS  
 P9ME  
 P9ML  
 P9MM  
 P9MC  
 P9MSC  
 P9MPS

Suitable for Product Class Pilot Devices

**Environmental**

Ambient Air Temperature Operation -25 ... +70 °C  
 Storage -40 ... +85 °C  
 Degree of Protection Front IP66  
 Housing IP66  
 Material Plastic

**Material Compliance**

Conflict Minerals Reporting Template (CMRT) 9AKK108467A5658  
 REACH Declaration 2CMT2022-006479  
 RoHS Information 2CMT2022-006498  
 RoHS Status Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019  
 Toxic Substances Control Act - TSCA 2CMT2023-006523  
 WEEE Category Product Not in WEEE Scope

**Certificates and Declarations**

cULus Certificate 9AKK107046A9925  
 Declaration of Conformity - CE 2CMT2015-005444  
 Declaration of Conformity - UKCA 2CMT2020-006121  
 DNV GL Certificate E-14107

**Container Information**

Package Level 1 Units bag 1 piece  
 Package Level 1 Width 0.11 m  
 Package Level 1 Depth / 0.35 m

Length

Package Level 1 Height	0.061 m
Package Level 1 Gross Weight	0.4 kg
Package Level 1 EAN	7320500312773

**Classifications**

eClass	V11.0 : 27371205
E-Number (Finland)	2339556
E-Number (Norway)	4373046
E-Number (Sweden)	3717110
ETIM 6	EC000200 - Enclosure for control circuit devices
ETIM 7	EC000200 - Enclosure for control circuit devices
ETIM 8	EC000200 - Enclosure for control circuit devices
ETIM 9	EC000200 - Enclosure for control circuit devices
IDEA Granular Category Code (IGCC)	4478 >> Electrical pushbutton enclosure
Object Classification Code	S
UNSPSC	39121326

**Categories**

Low Voltage Products and Systems → Control Products → Pilot Devices → Enclosures and Assembled Stations  
 Medium Voltage Products and Systems → Service → Spares and Consumables → Parts → All Spare Parts (Relays-SWG-CB)

