



PRODUCT-DETAILS

OHB125L12

OHB125L12 HANDLE



General Information

Extended Product Type	OHB125L12
Product ID	1SCA022577R7350
EAN	6417019186979
Catalog Description	OHB125L12 HANDLE
Long Description	OHB125L12 PISTOL HANDLE

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SCC011021D0201
RoHS Information	1SCC011020D0201
RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Ordering

Minimum Order Quantity	1 piece
------------------------	---------

Customs Tariff Number	85389099
Country of Origin	Estonia (EE)

Popular Downloads

Data Sheet, Technical Information	1SCC301020C0201
Instructions and Manuals	1SCC390022M0020

Dimensions

Product Net Width	158 mm
Product Net Height	45 mm
Product Net Depth / Length	66 mm
Product Net Weight	0.165 kg

Technical

Handle Color	Black
Handle Length	125 mm
Handle Type	Pistol
Special Functions	L12
Color	Black
Degree of Protection	IP66
Lock Type	Yes

Certificates and Declarations

Declaration of Conformity - CE	1SCC390030D2704
--------------------------------	-----------------

Container Information

Package Level 1 Units	bag 1 piece
Package Level 1 Width	50 mm
Package Level 1 Depth / Length	160 mm
Package Level 1 Height	70 mm
Package Level 1 Gross Weight	0.17 kg
Package Level 1 EAN	6417019186979

Classifications

Object Classification Code	N/A
ETIM 8	EC000229 - Handle for power circuit breaker
ETIM 9	EC000229 - Handle for power circuit breaker
UNSPSC	31162801
IDEA Granular Category Code (IGCC)	3038 >> Handles or knobs

eClass

V11.1 : 27370414

WEEE Category

Product Not in WEEE Scope

Categories

Low Voltage Products and Systems → Switches → DC Switch-Disconnectors

Low Voltage Products and Systems → Switches → Switch Disconnectors

Low Voltage Products and Systems → Switches → Switch Fuses → Accessories for Switch Fuses

