

Signal towers



KL70-401B

1SFC151607P001



KL70-401Y

1SFC151608P001



KA4-102...

1SFC151609P001

6

Description

Colors	Red	Green	Yellow	Blue	Clear
Replace <input checked="" type="checkbox"/> in type with	R	G	Y	L	C
Replace <input type="checkbox"/> in order code with	1	2	3	4	8

Description	Type	Order code	Pkg qty	Weight (1 pce) Kg
-------------	------	------------	---------	-------------------

Light element

Available in red, green, yellow, blue and clear

Permanent light, 12-240 V AC/DC For bulb BA 15d. Bulb not included	KL70-401	1SFA616070R401	1	0.09
Blinking light, 24 V AC/DC with integrated LED	KL70-306	1SFA616070R306	1	0.10
Flashing light, 24 V AC/DC with integrated xenon tube	KL70-203	1SFA616070R203	1	0.12
Blinking light, 115 V AC with integrated LED	KL70-342	1SFA616070R342	1	0.10
Flashing light, 115 V AC with integrated xenon tube	KL70-113	1SFA616070R113	1	0.11
Blinking light, 230 V AC with integrated LED	KL70-352	1SFA616070R352	1	0.10
Flashing light, 230 V AC with integrated xenon tube	KL70-123	1SFA616070R123	1	0.11
LED permanent light, 24 V AC/DC with integrated LED	KL70-305	1SFA616070R305	1	0.10
LED rotating light, 24 V AC/DC with integrated LED	KL70-307	1SFA616070R307	1	0.10

Bulbs: Bulb Ba 15d, 42mm, max 7 W for permanent or blinking light

24 V, 5 W, AC/DC	KA4-1021	1SFA616923R1028	10	0.009
115 V, 5 W, AC/DC	KA4-1118	1SFA616923R1118	10	0.009
230 V, 5 W, AC/DC	KA4-1148	1SFA616923R1148	10	0.009

LED bulbs Ba 15d, 40mA

Available in red, green, yellow, blue and white

24 V AC/DC	KA4-102	1SFA616924R102	1	0.009
------------	---------	----------------	---	-------

Audible modules buzzer element. 85 dB, continuous or pulsating tone, adjustable

24 V AC/DC	KB70-3001	1SFA616071R3001	1	0.11
115 V AC	KB70-3101	1SFA616071R3101	1	0.11
230 V AC	KB70-1201	1SFA616071R1201	1	0.12

