

CP600-eCo, CP600 and CP600-Pro

Key features

Various options for tailor made HMI solutions:

- PB610 Panel Builder 600 HMI applications
- Visualization of AC500 web servers
- Mobile remote access to HMI applications
- PB610-R PC runtime for Windows platforms
- Drivers for integration into automation systems
- OPC UA client and server



- CP600 brilliant colored display
- Aluminium enclosure
- Seven different screen sizes

- CP600-Pro multi-touch
- Brilliant real glass screen
- Aluminium enclosure
- Fast ETH 10/100/1000
- Operating temp.: -20...+60 °C
- Five different screen sizes from 5" to 21.5"

- CP600-eCo slim design for easy installation even in compact spaces
- Robust plastic enclosure
- Three different screen sizes

CP600-eCo, CP600 and CP600-Pro

Ordering data

CP600-eCo control panels

Display size	Resolution pixels	Description	Type	Order code	Price	Weight (1 pce) kg
4.3"	480 x 272	for PB610 applications or visualization of AC500 V3 web server	CP604	1SAP504100R0001		0.400
7.0"	800 x 480	for PB610 applications or visualization of AC500 V3 web server	CP607	1SAP507100R0001		0.600
10.1"	1024 x 600	for PB610 applications or visualization of AC500 V3 web server	CP610	1SAP510100R0001		1.000
4.3"	480 x 272	black, for PB610 applications or visualization of AC500 V3 web server	CP604-B	1SAP504100R2001		0.400
7.0"	800 x 480	black, for PB610 applications or visualization of AC500 V3 web server	CP607-B	1SAP507100R2001		0.600
10.1"	1024 x 600	black, for PB610 applications or visualization of AC500 V3 web server	CP610-B	1SAP510100R2001		1.000

Visualization of AC500 V3 web server is supported by products with revision index C1 or higher.



CP604



CP607



CP610



CP607-B

CP600 control panels

Display size	Resolution pixels	Description	Type	Order code	Price	Weight (1 pce) kg
4.3"	480 x 272	for PB610 Panel Builder 600 applications	CP620	1SAP520100R0001		0.950
4.3"	480 x 272	for visualization of AC500 V2 web server	CP620-WEB	1SAP520200R0001		0.950
5.7"	320 x 240	for PB610 Panel Builder 600 applications	CP630	1SAP530100R0001		1.150
5.7"	320 x 240	for visualization of AC500 V2 web server	CP630-WEB	1SAP530200R0001		1.150
7.0"	800 x 480	for PB610 Panel Builder 600 applications	CP635	1SAP535100R0001		1.100
7.0"	800 x 480	black, for PB610 Panel Builder 600 applications	CP635-B (*)	1SAP535100R2001		1.100
7.0"	800 x 480	for visualization of AC500 V2 web server	CP635-WEB	1SAP535200R0001		1.100
10.4"	800 x 600	for PB610 Panel Builder 600 applications	CP651	1SAP551100R0001		2.100
10.4"	800 x 600	for visualization of AC500 V2 web server	CP651-WEB	1SAP551200R0001		2.100
12.1"	800 x 600	for PB610 Panel Builder 600 applications	CP661	1SAP561100R0001		2.800
12.1"	800 x 600	for visualization of AC500 V2 web server	CP661-WEB	1SAP561200R0001		2.800
13.3"	1280 x 800	for PB610 Panel Builder 600 applications	CP665	1SAP565100R0001		2.600
13.3"	1280 x 800	for visualization of AC500 V2 web server	CP665-WEB	1SAP565200R0001		2.600
15"	1024 x 768	for PB610 Panel Builder 600 applications	CP676	1SAP576100R0001		3.800
15"	1024 x 768	for visualization of AC500 V2 web server	CP676-WEB	1SAP576200R0001		3.800

(*) Other control panels with black front on request.



CP635



CP651



CP665



CP635-B