

### General Information

Extended Product Type:	MSMNO
Product ID:	1SAM101923R0012
EAN:	4013614405341
Catalog Description:	MSMNO Driver
Long Description:	MSMNO Driver w/o coding w. screw for manual motor starters, 6x6

### Categories

Products » Low Voltage Products and Systems » Control Products » Manual Motor Starters » Manual Motor Starters Accessories

### Ordering

EAN:	4013614405341
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85369085

### Container Information

Package Level 1 Width:	143 mm
Package Level 1 Length:	60 mm
Package Level 1 Height:	112 mm
Package Level 1 Gross Weight:	1.7 g
Package Level 1 Units:	1 piece
Package Level 2 EAN:	4013614409820
Package Level 2 Units:	10 piece

### Dimensions

Product Net Weight:	1.7 g
---------------------	-------

### Technical

Shaft Diameter:	6x6 mm
Shaft Length:	32 mm
Tightening Torque:	0.12 N·m
Product Name:	Driver
Suitable For:	MS116 MS132 MS325 MO325
Suitable for Product Class:	Manual Motor Starter

### Environmental

RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
--------------	---

### Technical UL/CSA

Tightening Torque UL/CSA:	1.06 in·lb
---------------------------	------------

### Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	NoDecNee
---------------------------------	----------

### Classifications

eClass:	7.0 27379201
E-number:	3112085
UNSPSC:	39120000

