

# Single Ended Cordsets

## 90° Connector



Connector	Type	Model	Position	Cable Length	Part Number
M8	F	90°	3	5 m	08FA3C5Z
M8	M	90°	3	5 m	08MA3C5Z
M8	F	90°	4	5 m	08FA4C5Z
M8	M	90°	4	5 m	08MA4C5Z

### General Product Description

Description	M8 male/female 90° connector with cable, 3/4 positions
Connector Type	Male/Female
Number of Positions	3/4 poles
Connector Housing Color	Black
LED Indication	NA
Circuit Type	NA
Switching Status LED	NA
Voltage Status LED	NA
Cable Type	PUR
Cable Color	Black
Cable Length	
Wire Size	AWG 24

### Technical Data

Rated Voltage	60 V AC/DC
Rated Current	4 A

### Materials

Connector Contact Material	Phosphorous Bronze
Connector Contact Plating	AU Gold Plating
Connector Housing Material	Nylon 6+30% Glass Fibre
Connector Coupling Nut Material	Zn Al/Ni

### Environmental Ratings

Operating Temperature Range	-25°C to +70°C
Protection Rating	IP 69K

Package Quantity	1
------------------	---

### Notes:

Other variations available. Including PVC cable, custom cable length and color.

