

spiralblock CABLE GLANDS

Polyamide PA6.6



1500



spiralblock[®] standard

Metric thread M 1.5 pitch CEI EN 60423 CEI EN 50262

Ref. Light Grey	P	Fixing Hole \varnothing (mm)	\varnothing A min-max (mm)	B Spanner (mm)	C (mm)	L (mm)	Quantity
1500.M12	M12X1,5	12,5	3,5- 7	15	8	57	100
1500.M16	M16X1,5	16,5	5 -10	19	8	79	50
1500.M20	M20X1,5	20,5	7 -13	25	9	90	25
1500.M25	M25X1,5	25,5	10 -17	30	10	120	20
1500.M32	M32X1,5	32,5	13 -21	36	10	140	10

Add to Ref. N for Black

spiralblock[®] standard

Pg thread DIN 40 430

Ref. Light Grey	P	Fixing Hole \varnothing (mm)	\varnothing A min-max (mm)	B Spanner (mm)	C (mm)	L (mm)	Quantity
1500.07	Pg 7	12,5	3,5- 7	15	8	57	100
1500.09	Pg 9	15,5	5 - 8	19	8	68	100
1500.11	Pg11	19	5 -10	22	8	80	50
1500.13	Pg13,5	20,5	7 -12	24	10	90	50
1500.16	Pg16	22,5	10 -14	27	10	100	25
1500.21	Pg21	29	13 -18	33	12	112	20

Add to Ref. N for Black

spiralblock[®] standard

BSP thread ISO 228/1

Ref. Light Grey	P	Fixing Hole \varnothing (mm)	\varnothing A min-max (mm)	B Spanner (mm)	C (mm)	L (mm)	Quantity
1500.14	G1/4"	13,5	3- 6,5	15	8	57	100
1500.38	G3/8"	17	4- 8	19	9	68	100
1500.12	G1/2"	21,5	7-12	24	10	90	50
1500.34	G3/4"	27	13-18	33	12	112	20

Add to Ref. N for Black

Material: POLYAMIDE PA6.6 self-extinguishing class V2 (UL 94)
 Temperature range: -20°C to +90°C (continuous)
 Sealing ring: NEOPRENE[®] 50 sh A
 Protection: IP 68
 Colour: RAL 7035 light grey, RAL 9005 black

