



**Pg thread DIN 40 430 - Dimensions DIN 46 320**

Ref. Light Grey	P	Facing Hole Ø (mm)	Ø A min-max (mm)	B1 Spanner (mm)	B2 Spanner (mm)	C (mm)	L min-max (mm)	Quantity Box/Bag
1709	Pg 7	12.5	5.5- 7	15	16	8	16-20	300/100
* 1700	Pg 9	15.5	6.5- 8.5	17	20	8	19-22	200/100
* 1701	Pg11	19	8 -10	19	22	8	21-25	100/100
* 1702	Pg13.5	20.5	8 -11	21	24	9	22-26	100/100
1703	Pg16	22.5	11 -14	23	27	10	24-33	50/50
1704	Pg21	29	14.5-18	30	33	11	25-32	50/25
1705	Pg29	37	19 -26	40	42	11	27-32	20/10
1706	Pg36	47	30 -34	50	53	14	33-42	10/10
1707	Pg42	54	30 -38	55	60	13	37-48	10/5
1708	Pg48	60	38 -44	60	65	14.5	37-48	5/5

\*Add to Ref: N for Black

Material: POLYAMIDE PA6 self-extinguishing class VO (UL 94)  
Temperature range: -20°C to +90°C (continuous)  
Sealing ring: PVC 50 sh A  
Protection: IP 54  
Colour: RAL 7035 light grey, RAL 9005 black

**BSP thread ISO 228/1**

Ref. Light Grey	P	Facing Hole Ø (mm)	Ø A min-max (mm)	B1 Spanner (mm)	B2 Spanner (mm)	C (mm)	L min-max (mm)	Quantity Box/Bag
1400	G1/4"	13.5	5.5- 7	15	16	8	16-20	300/100
* 1401	G3/8"	17	6.5- 8.5	17	20	8	19-22	200/100
* 1401B	G3/8"	17	8 -10	19	22	8	18-24	100/100
* 1401C	G3/8"	17	10 -12	22	24	9	22-26	100/100
* 1402	G1/2"	21.5	8 -11	21	24	9	22-26	100/100
1403	G5/8"	23.5	11 -14	23	27	10	24-33	50/50
1404	G3/4"	27	14.5-18	30	33	11	25-32	50/25
1405	G1"	34	17 -22	34	38	11.5	27-35	20/10
1407	G1 1/2"	48	30 -34	50	53	14	33-42	10/10
1408	G2"	60	38 -44	60	65	14.5	37-48	5/5

\*Add to Ref: N for Black

**Metric thread M 1.5 pitch CE EN 60423**

Ref. Light Grey	P	Facing Hole Ø (mm)	Ø A min-max (mm)	B1 Spanner (mm)	B2 Spanner (mm)	C (mm)	L min-max (mm)	Quantity
1730M20	M20X1.5	20.5	8-11	21	24	9	22-26	100

Add to Ref: N for Black

