



Cable Glands

Sealing ring: PVC 50 sh A - Protection: IP 54

Pg thread DIN 40 430 - Dimensions DIN 46 320

Ref. Light: Grey	P	Facing Hole Ø (mm)	Ø A min-max (mm)	B1 Spanner (mm)	B2 Spanner (mm)	C (mm)	L min-max (mm)	Quantity Box/Bag
1700P	Pg9	15,5	7 - 8,5	17	20	8	19-22	200/100
* 1701P	Pg11	19	8 - 10	19	22	8	21-25	100/100
* 1702P	Pg13,5	20,5	8 - 11	21	24	9	22-26	100/100
1703P	Pg16	22,5	11 - 14	24	27	10	24-33	50/50
1704P	Pg21	29	14,5-18	30	33	11	25-32	50/25

*Add to Ref: N for Black

Material: POLYSTYRENE PS
Temperature range:
-20°C to +60°C (continuous)
Colour: RAL 7035 light grey,
RAL 9005 black

