

2053  
2052  
2021

## Entry plugs

### Metric thread M 1.5 pitch CEI EN 60423

Ref. Nickel Plated Brass	P	Ø A (mm)	C (mm)	Quantity Box/Bag
2053M12N	M12X1,5	14	5	1,500/100
2053M16N	M16X1,5	18	5	1,000/100
2053M20N	M20X1,5	22	6,5	500/100
2053M25N	M25X1,5	28	7	200/100
2053M32N	M32X1,5	35	8	150/50
2053M40N	M40X1,5	44	8,5	100/50
2053M50N	M50X1,5	54	9	50/25
2053M63N	M63X1,5	67	10	25/25

### Pg thread DIN 40 430 - Dimensions DIN 46 320

Ref. Nickel Plated Brass	P	Ø A (mm)	C (mm)	Quantity Box/Bag
2052007N	Pg 7	14	5	1,500/100
2052009N	Pg 9	17	6	1,000/100
2052011N	Pg11	20	6	500/100
2052013N	Pg13,5	22	6,5	500/100
2052016N	Pg16	24	6,5	500/100
2052021N	Pg21	30	7	200/50
2052029N	Pg29	38	8	100/25
2052036N	Pg36	50	9	50/50
2052042N	Pg42	57	10	25/25
2052048N	Pg48	64	10	25/25

## Entry bushes

### BSP thread ISO 228/1

Ref. Brass	P	Ø A (mm)	B Spanner (mm)	C (mm)	L (mm)	Quantity Box/Bag
2021014	61/4"	10	13	6	8,5	1,000/100
2021038	63/8"	12	17	7,5	10,5	800/100
2021012	61/2"	16	21	9,5	13	400/100
2021058	65/8"	18	23	10	13,5	250/50
2021034	63/4"	21	27	10	14	200/50
2021100	61"	26,5	34	11	15,5	100/50
2021118	61 1/8"	31	38	12	16,5	100/25
2021114	61 1/4"	35	42	13	18	50/25
2021112	61 1/2"	41,5	48	13	18,5	50/25
2021200	62"	51,5	60	13,5	19,5	25/25

Add to Ref. N for NICKEL PLATED BRASS



Material: Entry plugs - NICKEL PLATED BRASS (CuZn 40 Pb 3)  
Entry bushes - PLAIN BRASS  
Protection: Entry plugs - IP 54

