





**SQN125 - SQN160 SERIES** | EN 60529 - IP65 - UL50 Type 1 - 4 - 4x -12 (◆) Protection NEMA 4x.

### ACTUATORS






- Grey Plate
- Black knob
- Locking Facility (Max 3 locks)

SERIES	FRONT PLATE SIZE	PANEL MOUNTING TYPE R CODE	DOOR LOCKING TYPE B CODE ▶	LEGEND PLATE
SQ040 - SQ063 (6 poles)	ø78	309/0001	311/0001	
SQ125 - SQ160 (3, 6 poles)		309/0008	311/0008	






- Yellow Plate
- Red knob
- Locking Facility (Max 3 locks)

SERIES	FRONT PLATE SIZE	PANEL MOUNTING TYPE R CODE	DOOR LOCKING TYPE B CODE ▶	LEGEND PLATE
SQ040 - SQ063 (6 poles)	ø78	310/0001	312/0001	
SQ125 - SQ160 (3, 6 poles)		310/0008	312/0008	




- Grey Plate
- Black knob
- Locking Facility (Max 3 locks)

SERIES	FRONT PLATE SIZE	PANEL MOUNTING TYPE R CODE	DOOR LOCKING TYPE B CODE ▶	LEGEND PLATE
SQ040 - SQ063 (3 poles)	□67	319/0001 ◆	321/0001	
SQ125 - SQ160 (3, 6 poles)		319/0008 ◆	321/0008	



- Yellow Plate
- Red knob
- Locking Facility (Max 3 locks)

SERIES	FRONT PLATE SIZE	PANEL MOUNTING TYPE R CODE	DOOR LOCKING TYPE B CODE ▶	LEGEND PLATE
SQ040 - SQ063 (3 poles) 321, 322 Only	□67	320/0001 ◆	322/0001	
SQ125 - SQ160 (3, 6 poles)		320/0008 ◆	322/0008	