



Stainless Steel 303 (X8 CrNiS 18-9)
Stainless Steel 316L (X2 CrNiMo 17-12-2)




MAXinox Stainless Steel AISI 303

Pg thread DIN 40 430

Stainless Steel AISI 303	P	Fixing Hole Ø (mm)	Ø A min-max (mm)	B Spanner (mm)	E (mm)	C (mm)	L min-max (mm)	Quantity Box/Bag
7900.07	Pg 7	12.7	3 - 7	16	18	5.0	16-20	90/30
7900.09	Pg 9	15.5	4 - 8	17	19	6.0	17-23	90/30
7900.11	Pg11	18.8	4.5-10	20	23	6.0	20-25	60/30
7900.13	Pg13.5	20.5	5 -12	22	25	6.5	20-26	90/30
7900.16	Pg16	22.6	7 -13	24	27	6.5	20-27	60/30
7900.21	Pg21	28.5	10 -17	30	33	7.0	24-30	40/20
7900.29	Pg29	37.2	17 -25	40	45	8.0	30-37	30/15
7900.36	Pg36	47.2	20 -32	50	55	8.0	38-48	10
7900.42	Pg42	54.2	28 -38	57	63	10.0	36-46	5
7900.48	Pg48	60.0	34 -45	67	74	15.0	40-52	5

Material: STAINLESS STEEL 303/316L
Sealing-ring: NEOPRENE®
Cable grip insert: POLIAMMIDE PA6.6
O-Ring: NITRILE 70 sh A (factory fitted)
Protection: IP 68
Temperature range: -25°C to +100°C (continuous)



MAXinox Stainless Steel AISI 316L

Pg thread DIN 40 430

Stainless Steel AISI 316L	P	Fixing Hole Ø (mm)	Ø A min-max (mm)	B Spanner (mm)	E (mm)	C (mm)	L min-max (mm)	Quantity Box/Bag
7900A.07	Pg 7	12.7	3 - 7	16	18	5.0	16-20	60/20
7900A.09	Pg 9	15.5	4 - 8	17	19	6.0	17-23	60/20
7900A.11	Pg11	18.8	4.5-10	20	23	6.0	20-25	100/20
7900A.13	Pg13.5	20.5	5 -12	22	25	6.5	20-26	100/20
7900A.16	Pg16	22.6	7 -13	24	27	6.5	20-27	40/20
7900A.21	Pg21	28.5	10 -17	30	33	7.0	24-30	60/15
7900A.29	Pg29	37.2	17 -25	40	45	8.0	30-37	20/15
7900A.36	Pg36	47.2	20 -32	50	55	8.0	38-48	7
7900A.42	Pg42	54.2	28 -38	57	63	10.0	36-46	5
7900A.48	Pg48	60.0	34 -45	67	74	15.0	40-52	5