



Order #: ASI011178

4 level sensor/actuator DIN rail mounted terminal block with 3 feed through connections and 1 ground connection.

Technical Information

Current Rating (A):	34 A
Dimensions (L x W x H):	86x6.2x103.5mm (3.386x0.244x4.075")
DIN Rail Block Type:	Sensor Connection
Number Of Connections:	7
Number of Levels:	4 levels
Voltage (V):	400 V
Wire Connection Type:	Screw Clamp
Wire Size (AWG):	24-14 AWG
Wire Stripping Length:	8 mm (0.315")