



Terminal Width: 6.2mm

SPECIFICATIONS

Wire Size (AWG)	30 - 10
Current Rating	30A
Voltage Rating	600V
Dimensions (LxH) (mm)	42.5 x 47

ACCESSORIES

ORDER

End Cover	ASIDUK410
Circuit Bridges	
Internal with Screws - 10 position	ASIFB1106
External	
2 position	ASIEB26
3 position	ASIEB36
10 position	ASIEB106
Push-in - 10 position	ASIUFBS106
Separating Plate	ASITSK
Partition Plate	ASIATPUK
TB Markers	
Blank	ASIZB610B
Pre-printed 1-10 vert	ASIZB61010V
Pre-printed 1-10 horz	ASIZB61010H
Custom	ASIZB6C....
End Stop (Snap On) - Black	ASIUD1B
DIN Rail (2 meters)	
7.5 x 35mm slotted	PR005
7.5 x 35mm non-slotted	PR003
15 x 35mm slotted	PR006
15x 35mm non-slotted	PR007