


Certification	
	
Material	
Screw	M2.5 Steel, Tin Plated
Clamp	Brass, Nickel Plated
Housing	Polyamide66, White
Electrical	
Standard	UL 1059/CSA C22.2 No. 158
Rated Voltage	600 V
Rated Current	20 A
Wire Range	20-12 AWG
Mechanical	
Temperature Range	-40°C...+105°C
Torque	0.4N-m (3.6lb-in)
Strip Length	7-8 mm (0.26-0.31")
Size	
Pitch	8 mm (.315")
Poles	2P-12P. Additional sizes available on request.

Item	No. of Poles	Length (mm)
ASIMY8HW+1.2-8.0-2P	2	14.0
ASIMY8HW+1.2-8.0-3P	3	22.0
ASIMY8HW+1.2-8.0-4P	4	30.0
ASIMY8HW+1.2-8.0-5P	5	38.0
ASIMY8HW+1.2-8.0-6P	6	46.0
ASIMY8HW+1.2-8.0-7P	7	54.0
ASIMY8HW+1.2-8.0-8P	8	62.0
ASIMY8HW+1.2-8.0-9P	9	70.0
ASIMY8HW+1.2-8.0-10P	10	78.0
ASIMY8HW+1.2-8.0-11P	11	86.0
ASIMY8HW+1.2-8.0-12P	12	94.0