



**ASIUK3MVSTB508**

## SPECIFICATIONS

Wire Range, AWG	26-12
Current Rating	12A
Voltage Rating	250V
Dimensions (mm)	47X42.5X5.08mm

## ACCESSORIES

<b>End Stop (snap-on)</b> Black	ASIUD1B	25
<b>DIN Rail (2 meters)</b>		
7.5 x 35mm slotted	PR005	1
7.5 x 35mm non-slotted	PR003	1
15 x 35mm slotted	PR006	1
15 x 35mm non-slotted	PR007	1