



- Slide-on technology for secure installation on standard DIN rails
- Interlocking feature for additional stability
- Center snap in labelling strip allows for easy circuit identification to simplify wiring
- Snap on covers provide total insulation and side jumpers ease circuit cross connection
- Locking washer for assured connection
- Multiple wire models for power distribution and double levels for space saving are available
- Models are UL approved, 10 to 309 amps, 600V

Ordering Info		
Order #	ASI391009	ASI391010
Type	ASIUTD-200	ASIUTD-300
Specifications		
Dimensions (DxWxH) mm	83.4/39/57.5	86/46/62.5
Screw Size	M10	M10
Voltage Rating (V)	600	600
Current Rating (Amps)	240	309
Color	Black	Black

Accessories		
	Order #	Order #
End Stop	ASIUD1B	ASIUD1B
DIN Rail 7.5 x 35mm slotted	PR005	PR005
Dust Cover	ASI395005	ASI395005
Marking Label	ASI394006	ASI394006