



- Slide-On technology for secure installation on standard DIN rails
- Interlocking feature for additional stability
- Center snap in labelling strip allows for easy circuit identification to simplify wiring
- Snap on covers provide total insulation and side jumpers ease circuit cross connection
- Locking washer for assured connection
- Multiple wire models for power distribution and double levels for space saving are available
- Models are UL approved, 10 to 309 amps, 600V

Ordering Info			
<b>Order #</b>	ASI391006	ASI391007	ASI391008
<b>Type</b>	ASIUTD-63	ASIUTD-100	ASIUTD-150
Specifications			
<b>Dimensions (DxWxH) mm</b>	54/19.5/38	72/27/45	76/28/51
<b>Screw Size</b>	M6	M8	M8
<b>Voltage Rating (V)</b>	600	600	600
<b>Current Rating (Amps)</b>	90	130	175
<b>Color</b>	Black	Black	Black

Accessories			
	Order #	Order #	Order #
<b>End Stop</b>	ASIUD1B	ASIUD1B	ASIUD1B
<b>DIN Rail (2 Meters)</b> 7.5 x 35mm slotted 7.5 x 35mm non-slotted 15 x 35mm slotted 15 x 35mm non-slotted	PR005 PR003 PR006 PR007	PR005 PR003 PR006 PR007	PR005 PR003 PR006 PR007
<b>Marking Label</b>	ASI394006	ASI394006	ASI394006
<b>Dust Cover</b>	ASI395003	ASI395004	ASI395004
<b>End Cover</b>	ASI392003	ASI392004	ASI392005