


Certification	
	
Material	
Screw	M2.5, Steel Zinc Plated
Cage	Brass, Nickel Plated
Applicator	Steel, Zinc Plated
Pin/Plate	Brass, Tin Plated
Housing	PA66, UL 94V-0, Green
Electrical	
Standard	UL 1059/CSA C22.2 No. 158
Rated Voltage	300 V
Rated Current	15 A
Wire Range	30-14 AWG
Contact Resistance	20m Ω
Insulation Resistance	500M Ω /500 Vdc
Withstand Voltage	2000 Vac/1 Min
Mechanical	
Temperature Range	-40°C...+105°C
Torque	0.4N-m (3.5lb-in)
Strip Length	12-13 mm (0.47-0.51")
Size	
Pitch	5.0 mm (.197")
Poles	2P-12P. Additional sizes available on request.

Item	No. of Poles	Length (mm)
ASIWJ105V-5.0-2P	2	12.5
ASIWJ105V-5.0-3P	3	17.5
ASIWJ105V-5.0-4P	4	22.5
ASIWJ105V-5.0-5P	5	27.5
ASIWJ105V-5.0-6P	6	32.5
ASIWJ105V-5.0-7P	7	37.5
ASIWJ105V-5.0-8P	8	42.5
ASIWJ105V-5.0-9P	9	47.5
ASIWJ105V-5.0-10P	10	52.5
ASIWJ105V-5.0-11P	11	57.5
ASIWJ105V-5.0-12P	12	62.5