


Certification	
	
Material	
Spring	Stainless Steel
Pin/Plate	Brass, Tin Plated
Housing	PA66, UL 94V-0, Green
Electrical	
Standard	UL 1059/CSA C22.2 No. 158
Rated Voltage	150 V
Rated Current	4 A
Wire Range	26-18 AWG
Contact Resistance	20m Ω
Insulation Resistance	500M Ω /500 Vdc
Withstand Voltage	1300 Vac/1 Min
Mechanical	
Temperature Range	-40°C...+105°C
Strip Length	9-10 mm (0.35-0.39")
Size	
Pitch	2.54 mm (.100")
Poles	2P-16P. Additional sizes available on request.

Item	No. of Poles	Length (mm)
ASIWJ141R-2.54-2P	2	7.62
ASIWJ141R-2.54-3P	3	10.16
ASIWJ141R-2.54-4P	4	12.7
ASIWJ141R-2.54-5P	5	15.24
ASIWJ141R-2.54-6P	6	17.78
ASIWJ141R-2.54-7P	7	20.32
ASIWJ141R-2.54-8P	8	22.86
ASIWJ141R-2.54-9P	9	25.4
ASIWJ141R-2.54-10P	10	27.94
ASIWJ141R-2.54-11P	11	30.48
ASIWJ141R-2.54-12P	12	33.02
ASIWJ141R-2.54-13P	13	35.56
ASIWJ141R-2.54-14P	14	38.1
ASIWJ141R-2.54-15P	15	40.64
ASIWJ141R-2.54-16P	16	43.18