


| Certification | |
|---|--|
|  | |
| Material | |
| Spring | Stainless Steel |
| Pin/Plate | Brass, Tin Plated |
| Housing | PA66, UL 94V-0, Green |
| Electrical | |
| Standard | UL 1059/CSA C22.2 No. 158 |
| Rated Voltage | 300 V |
| Rated Current | 10 A |
| Wire Range | 22-16 AWG |
| Contact Resistance | 20m Ω |
| Insulation Resistance | 500M Ω /500 Vdc |
| Withstand Voltage | 2000 Vac/1 Min |
| Mechanical | |
| Temperature Range | -40°C...+105°C |
| Strip Length | 9-10 mm (0.35-0.39") |
| Size | |
| Pitch | 7.62 mm (.300") |
| Poles | 2P-16P. Additional sizes available on request. |

| Item | No. of Poles | Length (mm) |
|--------------------|--------------|-------------|
| ASIWJ142R-7.62-2P | 2 | 17.78 |
| ASIWJ142R-7.62-3P | 3 | 25.4 |
| ASIWJ142R-7.62-4P | 4 | 33.02 |
| ASIWJ142R-7.62-5P | 5 | 40.64 |
| ASIWJ142R-7.62-6P | 6 | 48.26 |
| ASIWJ142R-7.62-7P | 7 | 61.88 |
| ASIWJ142R-7.62-8P | 8 | 69.5 |
| ASIWJ142R-7.62-9P | 9 | 77.12 |
| ASIWJ142R-7.62-10P | 10 | 84.74 |
| ASIWJ142R-7.62-11P | 11 | 92.36 |
| ASIWJ142R-7.62-12P | 12 | 99.98 |
| ASIWJ142R-7.62-13P | 13 | 107.6 |
| ASIWJ142R-7.62-14P | 14 | 115.2 |
| ASIWJ142R-7.62-15P | 15 | 122.84 |
| ASIWJ142R-7.62-16P | 16 | 130.46 |