



Certification	
Material	
Pin/Plate	Phosphor Bronze, Nickel Plated
Spring	Stainless Steel
Housing	PA66, UL 94V-0, Green
Electrical	
Standard	UL 1059/CSA C22.2 No. 158
Rated Voltage	300 V
Rated Current	10 A
Wire Range	28-14 AWG
Contact Resistance	20mΩ
Insulation Resistance	500MΩ/500 Vdc
Withstand Voltage	2000 Vac/1 Min
Mechanical	
Temperature Range	-40°C...+105°C
Strip Length	7-8 mm (0.28-0.31")
Size	
Pitch	5.08 mm (.200")
Poles	2P-16P. Additional sizes available on request.

Item	No. of Poles	Length (mm)
ASIWJ2EDGKD-5.08-2P	2	10.76
ASIWJ2EDGKD-5.08-3P	3	15.84
ASIWJ2EDGKD-5.08-4P	4	20.92
ASIWJ2EDGKD-5.08-5P	5	26.0
ASIWJ2EDGKD-5.08-6P	6	31.08
ASIWJ2EDGKD-5.08-7P	7	36.16
ASIWJ2EDGKD-5.08-8P	8	41.24
ASIWJ2EDGKD-5.08-9P	9	46.32
ASIWJ2EDGKD-5.08-10P	10	51.48
ASIWJ2EDGKD-5.08-11P	11	56.48
ASIWJ2EDGKD-5.08-12P	12	61.56
ASIWJ2EDGKD-5.08-13P	13	66.64
ASIWJ2EDGKD-5.08-14P	14	71.72
ASIWJ2EDGKD-5.08-15P	15	76.8
ASIWJ2EDGKD-5.08-16P	16	81.88