



Certification	
	UL [®] US
Material	
Lock Screw	M2.5 Steel, Tin Plated
Pin/Plate	Phosphor Bronze, Nickel Plated
Spring	Stainless Steel
Housing	PA66, UL 94V-0, Green
Electrical	
Standard	UL 1059/CSA C22.2 No. 158
Rated Voltage	300 V
Rated Current	10 A
Wire Range	28-14 AWG
Contact Resistance	20mΩ
Insulation Resistance	500MΩ/500 Vdc
Withstand Voltage	2000 Vac/1 Min
Mechanical	
Temperature Range	-40°C...+105°C
Strip Length	7-8 mm (0.28-0.31")
Size	
Pitch	5.08 mm (.200")
Poles	2P-16P. Additional sizes available on request.

Item	No. of Poles	Length (mm)
ASIWJ2EDGKDG-5.08-2P	2	22.76
ASIWJ2EDGKDG-5.08-3P	3	27.84
ASIWJ2EDGKDG-5.08-4P	4	32.92
ASIWJ2EDGKDG-5.08-5P	5	38.0
ASIWJ2EDGKDG-5.08-6P	6	43.08
ASIWJ2EDGKDG-5.08-7P	7	48.16
ASIWJ2EDGKDG-5.08-8P	8	53.24
ASIWJ2EDGKDG-5.08-9P	9	58.32
ASIWJ2EDGKDG-5.08-10P	10	63.4
ASIWJ2EDGKDG-5.08-11P	11	68.48
ASIWJ2EDGKDG-5.08-12P	12	73.56
ASIWJ2EDGKDG-5.08-13P	13	78.64
ASIWJ2EDGKDG-5.08-14P	14	83.72
ASIWJ2EDGKDG-5.08-15P	15	88.8
ASIWJ2EDGKDG-5.08-16P	16	93.88