



Certification	
Material	
Screw	M3.0 Steel, Tin Plated
Pin/Plate	Phosphor Bronze, Nickel Plated
Cage	Brass, Nickel Plated
Housing	PA66, UL 94V-0, Green
Electrical	
Standard	UL 1059/CSA C22.2 No. 158
Rated Voltage	300 V
Rated Current	15 A
Wire Range	28-14 AWG
Contact Resistance	20mΩ
Insulation Resistance	500MΩ/500 Vdc
Withstand Voltage	2000 Vac/1 Min
Mechanical	
Temperature Range	-40°C...+105°C
Torque	0.5N-m (4.4lb-in)
Strip Length	7-8 mm (0.28-0.31")
Size	
Pitch	5 mm (.197")
Poles	4P, 8P-16P. Additional sizes available on request.

Item	No. of Poles	Length (mm)
ASIWJ2EDGKZ-5.0-4P	4	20
ASIWJ2EDGKZ-5.0-8P	8	40
ASIWJ2EDGKZ-5.0-9P	9	45
ASIWJ2EDGKZ-5.0-10P	10	50
ASIWJ2EDGKZ-5.0-11P	11	55
ASIWJ2EDGKZ-5.0-12P	12	60
ASIWJ2EDGKZ-5.0-13P	13	65
ASIWJ2EDGKZ-5.0-14P	14	70
ASIWJ2EDGKZ-5.0-15P	15	75
ASIWJ2EDGKZ-5.0-16P	16	80