


Certification	
C  US	
Material	
Pin/Plate	Brass, Tin Plated
Housing	PA66, UL 94V-0, Green
Electrical	
Standard	UL 1059/CSA C22.2 No. 158
Rated Voltage	300 V
Rated Current	15 A
Contact Resistance	20mΩ
Insulation Resistance	500MΩ/500 Vdc
Withstand Voltage	2000 Vac/1 Min
Mechanical	
Temperature Range	-40°C...+105°C
Size	
Pitch	5.0 mm (.197")
Poles	2P-16P. Additional sizes available on request.

Item	No. of Poles	Length (mm)
ASIWJ2EDGVH-5.0-2P	2	11.6
ASIWJ2EDGVH-5.0-3P	3	16.6
ASIWJ2EDGVH-5.0-4P	4	21.6
ASIWJ2EDGVH-5.0-5P	5	26.6
ASIWJ2EDGVH-5.0-6P	6	31.6
ASIWJ2EDGVH-5.0-7P	7	36.6
ASIWJ2EDGVH-5.0-8P	8	41.6
ASIWJ2EDGVH-5.0-9P	9	46.6
ASIWJ2EDGVH-5.0-10P	10	51.6
ASIWJ2EDGVH-5.0-11P	11	56.6
ASIWJ2EDGVH-5.0-12P	12	61.6
ASIWJ2EDGVH-5.0-13P	13	66.6
ASIWJ2EDGVH-5.0-14P	14	71.6
ASIWJ2EDGVH-5.0-15P	15	76.6
ASIWJ2EDGVH-5.0-16P	16	81.6