



Certification	
Material	
Pin/Plate	Brass, Tin Plated
Housing	PA66, UL 94V-0, Green
Electrical	
Standard	UL 1059/CSA C22.2 No. 158
Rated Voltage	300 V
Rated Current	15 A
Contact Resistance	20mΩ
Insulation Resistance	500MΩ/500 Vdc
Withstand Voltage	2000 Vac/1 Min
Mechanical	
Temperature Range	-40°C...+105°C
Size	
Pitch	5.0 mm (.197")
Poles	2P-12P. Additional sizes available on request.

Item	No. of Poles	Length (mm)
ASIWJ2EDGVTC-5.0-2P	2	13.9
ASIWJ2EDGVTC-5.0-3P	3	18.9
ASIWJ2EDGVTC-5.0-4P	4	23.9
ASIWJ2EDGVTC-5.0-5P	5	28.9
ASIWJ2EDGVTC-5.0-6P	6	33.9
ASIWJ2EDGVTC-5.0-7P	7	38.9
ASIWJ2EDGVTC-5.0-8P	8	43.9
ASIWJ2EDGVTC-5.0-9P	9	48.9
ASIWJ2EDGVTC-5.0-10P	10	53.9
ASIWJ2EDGVTC-5.0-11P	11	58.9
ASIWJ2EDGVTC-5.0-12P	12	63.9