



Material		
Screw	M1.6, Steel Zinc Plated	
Cage	Copper Alloy, Nickel Plated	
Pin/Plate	Copper Alloy, Tin Plated	
Housing	PA66, UL 94V-0, Green	
Electrical		
Rated Voltage	150 V	
Rated Current	6 A	
Wire Range	26-18 AWG	
Contact Resistance	20m Ω	
Insulation Resistance	500M Ω /500 Vdc	
Withstand Voltage	1300 Vac/1 Min	
Mechanical		
Temperature Range	-40°C...+105°C	
Torque	0.1N-m (0.89lb-in)	
Strip Length	4-5 mm (0.16-0.20")	
Size		
Pitch	2.54 mm (.100")	
Poles	2P-12P. Additional sizes available on request.	

Item	No. of Poles	Length (mm)
ASIWJEK254-2.54-2P	2	5.54
ASIWJEK254-2.54-3P	3	8.08
ASIWJEK254-2.54-4P	4	10.62
ASIWJEK254-2.54-5P	5	13.16
ASIWJEK254-2.54-6P	6	15.7
ASIWJEK254-2.54-7P	7	18.24
ASIWJEK254-2.54-8P	8	20.78
ASIWJEK254-2.54-9P	9	23.32
ASIWJEK254-2.54-10P	10	25.86
ASIWJEK254-2.54-11P	11	28.4
ASIWJEK254-2.54-12P	12	30.94