


Certification	
	
Material	
Screw	M2.5, Steel Zinc Plated
Cage	Brass, Nickel Plated
Pin/Plate	Brass, Tin Plated
Housing	PA66, UL 94V-0, Green
Electrical	
Standard	UL 1059/CSA C22.2 No. 158
Rated Voltage	300 V
Rated Current	15 A
Wire Range	30-14 AWG
Contact Resistance	20mΩ
Insulation Resistance	500MΩ/500 Vdc
Withstand Voltage	2000 Vac/1 Min
Mechanical	
Temperature Range	-40°C...+105°C
Torque	0.4N-m (3.5lb-in)
Strip Length	6-7 mm (0.24-0.28")
Size	
Pitch	5.08 mm (.200")
Poles	2P-16P. Additional sizes available on request.

Item	No. of Poles	Length (mm)
ASIXD508-5.08-2P	2	11.06
ASIXD508-5.08-3P	3	16.14
ASIXD508-5.08-4P	4	21.22
ASIXD508-5.08-5P	5	26.3
ASIXD508-5.08-6P	6	31.38
ASIXD508-5.08-7P	7	36.46
ASIXD508-5.08-8P	8	41.54
ASIXD508-5.08-9P	9	46.62
ASIXD508-5.08-10P	10	51.7
ASIXD508-5.08-11P	11	56.78
ASIXD508-5.08-12P	12	61.86
ASIXD508-5.08-13P	13	66.94
ASIXD508-5.08-14P	14	72.02
ASIXD508-5.08-15P	15	77.1
ASIXD508-5.08-16P	16	82.18